



INNOVATE. PERFORM. STAND OUT.

De-Ionised Water
28 Day Immersion Testing











	Genable Dispersion in Epoxy Resin Vs. 20% Glass Flake			
Immersion Media (28 Days @ 23°C)	Genable 1200 Loading		Genable 1400 Loading	
	2.50%	5.00%	3.33%	6.67%
Visual Appearance	•		A	A
Blistering	I		_	-
Hardness Retention	A		A	
Gloss Retention	_	-//		(–







Proud to be a leading innovator in graphene dispersion and application technology