







Lactic Acid Hybrid 28 Day Immersion Testing



Immersion Media (28 Days @ 23°C)	Genable Dispersion + 10% Glass Flake in Epoxy Resin Vs. 20% Glass Flake	
	Genable 1200 Loading	Genable 1400 Loading
		2.50%
Visual Appearance	▲	▲
Blistering	▲	▲
Hardness Retention	▲	▲
Gloss Retention	▲	▲



Pencil Hardness Retention



Proud to be a leading innovator in graphene dispersion and application technology